

LSRII-Green Filter Configuration

Blue

Detector A 695/40	Detector B 530/30
PerCP	FITC
PerCP-Cy5.5	Alexa Fluor 488
PE-Cy5	GFP
	CFSE

Red

Detector A 780/60	Detector B 730/45	Detector C 660/20
APC-Cy7	Alexa Fluor 700	APC
APC-H7		Alexa Fluor 647
APC-efluor 780		Alexa Fluor 633
		Cy5

Violet

Detector A 780/60	Detector B 710/50	Detector C 650/20	Detector D 610/20	Detector E 525/50	Detector F 450/50
BV785	BV711	BV650	BV605	V500	Pacific Blue
Qdot 800	Qdot 705	Qdot 655	Qdot 605	AmCyan	efluor 450
				BV510	BV421
				Qdot 525	V450

Yellow-Green

Detector A 780/60	Detector B 660/40	Detector C 605/15	Detector D 582/15
PE-Cy7	PE-Cy5	PE-Texas Red	PE
	PE-Cy5.5	Alexa Fluor 594	Cy3
	7AAD	Alexa Fluor 568	dsRed
		Alexa Fluor 610	tdTomato
		mCherry	

Ultra-Violet

Detector A 740/35	Detector B 450/50	Detector C 379/28
BUV737	Alexa Fluor 350	BUV395
	Live/Dead Fix Blue	
	DAPI	
	Hoescht Blue	